

739000 - Sloan Letter Near Vision Answer Key

Testing distance of 30 cm

Letter Size	Decimal	LogMAR		Distance Equivalents		
				Foot	Meter	Diopters
6.0M	.05	1.3	C O H Z V	20/400	6/120	20D
4.7M	.063	1.2	S Z N D C	20/320	6/95	15D
3.7M	.06	1.1	V K C N R	20/250	6/75	12D
3.0M	.10	1.0	K C R H N	20/200	6/60	10D
2.4M	.12	0.9	Z K D V C	20/160	6/48	8D
1.8M	.16	0.8	H V O R K	20/125	6/38	6D
1.5M	.20	0.7	R H S O N	20/100	6/30	5D
.9M	.25	0.6	K S V R H	20/80	6/24	4D
.94M	.32	0.5	H N K C D	20/63	6/19	3D
.75M	.40	0.4	N D V K O	20/50	6/15	2.5D
.60M	.50	0.3	D H O S Z	20/40	6/12	
.47M	.63	0.2	V R N D O	20/32	6/9.5	
.37M	.80	0.1	C Z H K S	20/25	6/7.5	
.30M	1.0	0.0	O R Z S K	20/20	6/6	
.24M	1.25	-0.1	S C N D Z	20/16	6/4.8	
.19M	1.6	-0.2	N D H K C	20/12.5	6/3.8	
.15M	2.0	-0.3	V K O R H	20/10	6/3	

739000 - Sloan Letter Near Vision Answer Key

Testing distance of 30 cm

Letter Size	Decimal	LogMAR		Distance Equivalents		
				Foot	Meter	Diopters
6.0M	.05	1.3	Z R K D C	20/400	6/120	20D
4.7M	.063	1.2	D N C H V	20/320	6/95	15D
3.7M	.06	1.1	C D H N R	20/250	6/75	12D
3.0M	.10	1.0	R V Z O S	20/200	6/60	10D
2.4M	.12	0.9	O S D V Z	20/160	6/48	8D
1.8M	.16	0.8	N O Z C D	20/125	6/38	6D
1.5M	.20	0.7	R D N S K	20/100	6/30	5D
.9M	.25	0.6	O K S V Z	20/80	6/24	4D
.94M	.32	0.5	K S N H O	20/63	6/19	3D
.75M	.40	0.4	H O V S N	20/50	6/15	2.5D
.60M	.50	0.3	V C S Z H	20/40	6/12	
.47M	.63	0.2	C Z D R V	20/32	6/9.5	
.37M	.80	0.1	S H R Z C	20/25	6/7.5	
.30M	1.0	0.0	D N O K R	20/20	6/6	
.24M	1.25	-0.1	H Z S C V	20/16	6/4.8	
.19M	1.6	-0.2	C K R D Z	20/12.5	6/3.8	
.15M	2.0	-0.3	R D O N K	20/10	6/3	