




# Operating Guide



## TV Digital Connector for

# TV SoundBox®

TV-95 and TV-100 Listening Headsets

Model  
**DAC-202**


### SAFETY INSTRUCTIONS:

Please read these instructions carefully before using the DAC-202 TV Digital Connector.


- This product is for indoor use only.
- Do not open the housing. There are no user service-able parts in this product.
- Use only the AC adapter included with this product.

### PACKAGE CONTENT CHECK:

Your TV Digital Connector is packaged with all of the items shown. If anything is missing, please contact our Customer Care Department immediately.



### CONNECTORS:




### CONNECTION AND SET UP:

Please turn off all related audio and video devices before installation. Reactivate these devices only after all connections are complete.

#### Digital Optical Cable (TOSLINK) Connection:

1. Remove small plastic cover tips from both ends of the digital optical cable.
2. Slide the switch on the side of the DAC-202 to "OPTICAL". Please Note: Digital Optical cable is fragile. Do NOT bend the cable.
3. Connect the RCA ends of the audio cable (included with your TV SoundBox®) to the AUDIO R-L output of the DAC-202. Connect the other end to your TV.
4. Connect the AC adapter to the DC "in" of the digital connector and plug in the other end to your AC wall outlet.



### SPECIFICATIONS: (product may vary.)

Digital Optical Cable IN.....	E1AJ RC-5720B
(TOSLINK IN) Note: DAC-202 also	Rectangular type plug
Coaxial Cable IN.....	RCA Type Connector
LED Indication.....	Power
Audio Output.....	RCA Type RL
Audio Format Support.....	LPCM 44KHz, 96KHz
AC Adapter.....	5 VDC



All rights reserved. Marketed by Serene Innovations, Inc., Norwalk, CA  
Assembled in P.R.C. Manufactured by Trans Electric Co. LTD, Model DAC-200