


LA-277 Conference Microphone

The LA-277 Conference Microphone provides high quality audio pickup in all directions. It is designed to be used on a table or other flat surfaces. This is an ideal microphone for multiple users of one transmitter.



The LA-277 has an omni-directional pickup pattern. This means that audio from a broader area can be picked up by the microphone element. The main advantage of this type of microphone is that it does not have to be oriented directly towards your mouth for good audio pickup.

Using the LA-277 Conference Microphone

- Set the microphone sensitivity switch (located inside front cover of the LT-700 Portable FM Display Transmitter) to the HI position.
- Connect the microphone plug firmly to the microphone jack on the LT-700.
- Place the unit on the table, clear of any obstructions that might interfere with its pick up of voices. For best quality, users should be as close to the microphone as possible (the ideal range is 2 to 3 feet). The closer you are to the microphone, the better it will sound.

