



their safety is essential.

Products made to work hard—and built to last.

16-Gallon Gravity-Fed Eyewash Station

Don't risk safety, even in remote locations

This self-contained, standalone eyewash station is suitable wherever continuous water isn't available—no plumbing needed. The gravity-fed eyewash supplies a continuous, controlled flow that exceeds the ANSI Z358.1 standard of 1.5 LPM (0.4 GPM) for 15 minutes, providing a reliable safety solution no matter where you are located.

- Portable design with carrying handles and concealed mounting bracket make moving and relocating easy
- Can be wall mounted or used on a bench or tabletop
- High-visibility color is easy to identify in emergency situations
- Simple to use with pull-down activation handle
- Easy to maintain—wide fill opening enables quick inspection, cleaning and filling
- Meets ANSI Z358.1 and EN15154 requirements

Closed position allows easy access to pull-down activation handle.



The eyewash delivers an even spray to flush eyes completely.

For further information visit us online at hughes-safety-showers.com

Description	Capacity US Gallons / Liters	Operating Duration (min)	H x W x D	Water Flow per Minute US Gallons / Liters	Product Weight Full/Empty	Approv/Lstg Regulation*	Model
Gravity-fed eyewash station (one single unit)	16 / 60.5	15	25.12 x 21.26 x 11.3 in (638 x 540 x 287 mm)	0.55 / 2	141.7 lbs (64.3 kg) 19.8 lbs (9 kg)	AN, ENS	16GFEW
Gravity-fed eyewash station (one pallet of 12 units)			57 x 44 x 37 in (1449 x 1118 x 940 mm)		Empty weight: 283.52 lbs (128.6 kg)		16GFEWP

*AN = Meets or exceeds American National Standards Institute (ANSI) Z358.1; ENS = Complies with European standard for showers, EN15154

Additive Solution preserves water to eliminate bacteria and avoid additional eye damage. One bottle preserves up to 20 gallons of water for up to 120 days.

Description	Packaging	Model
Eyewash Additive (USA Version)	4 x 8 oz bottles, with FDA compliant label	ADDR4PKUS
Eyewash Additive (Canada Version)	4 x 8 oz bottles, with tri-lingual label	ADDR4PKCAN



For orders and sales support, contact:

Justrite Phone: +1-800-798-9250
Email: custserv@justrite.com